

Button Battery Sealing Machine For Button Batteries

Item Number: PC2NS



Introduction

KINTEK's Manual Button Battery Sealer ensures precise, airtight sealing for CR2032, LR44 batteries. Ideal for labs, R&D, and small production. Boost efficiency now!

[Learn More](#)

Instrument model	PC2NS
Pressure range	0-2T (0-25MPa)
Piston diameter	32mm(d) in chrome-plated oil cylinder
Pressure gauge	Digital display 0.00-40.00MPa
Standard mold	Standard CR20 series package mold
Sealing mold	Optional CR16, CR20, CR24, CR30, etc.
Sealing pressure	Generally between 0.8-1.2 tons
Shell removal mold	Optional CR16, CR20, CR24, CR30, etc.
Shell removal pressure	Generally within 0.4 tons
Overall dimensions	210*165*290mm(LX*W*H)
Equipment weight	12Kg
Machine size diagram	