

Button Battery Sealing Press Machine For Lab

Item Number: PP2N



Introduction

Boost button battery production with KINTEK's Electric Sealer – precision sealing, 300-600 pieces/hour, intelligent pressure control. Enhance yield now!

[Learn More](#)

Instrument model	PP2N
Pressure range	50-1500kg
Pressure-adding process	Program pressurization - program pressure maintenance - timed pressure release
Pressure-holding time	0-999 seconds
Pressure conversion	Program automatically converts the pressure that the mold can withstand
LCD display	4.3-inch LCD screen
Sealing mold	Optional CR16, CR20, CR24, CR30, etc.
Shell removal mold	Optional CR16, CR20, CR24, CR30, etc.
Standard mold	Standard CR20 series packaging mold
Dimensions	220*240*380(L*W*H)
Equipment power supply	220V(50Hz/60Hz)
Equipment weight	35kg
Machine size diagram	