

Lab Button Battery Disassembly And Sealing Mold

Item Number: PCKM



Introduction

KINTEK's precision button battery sealing molds ensure airtight, contamination-free results for labs and production. Boost efficiency with durable, high-performance solutions.

[Learn More](#)

Instrument model	Button battery removal mold	Button battery sealing mold
Disassembly die	CR16,CR20,CR24,CR30 optional	CR16,CR20,CR24,CR30 optional
Disassembly pressure		0.8-1.2Ton
Dimensions	Φ60*140mm(L*H)	Φ60X140mm(LXH)
Weight	1.85kg	1.85kg

Sealing mold size diagram