

Lab Button Battery Tablet Press Sealing Mold

Item Number: PMN



Introduction

Precision Sealing Die for button battery assembly & analysis. Durable hardened steel, CR16-CR30 compatible. Enhance battery integrity & performance. Get yours now!

[Learn More](#)

Instrument model	PMN
Dual-purpose mold	Sealing, opening and dual-use
Sealing function	CR16,CR20,CR24,CR30 optional
Sealing pressure	0.8-1.2 Ton
Dismantling function	CR16,CR20,CR24,CR30 optional
Dismantling pressure	
Diagram of hydraulic powder press size	