

Manual Button Battery Sealing Machine For Battery Sealing

Item Number: PC2N



Introduction

Manual Button Battery Sealer for precise, affordable lab sealing. Ideal for CR2032, LR44 batteries. Enhances safety & extends battery life. Get yours now!

[Learn More](#)

Instrument model	PC-2N
Pressure range	0-2T (0-25MPa)
Piston diameter	32mm(d) in chrome-plated oil cylinder
Pressure gauge	Dual scale display of pressure and pressure
Standard mold	Standard CR20 series package mold
Sealing mold	Optional CR16, CR20, CR24, CR30, etc.
Sealing pressure	Generally between 0.8-1.2 tons
Shell removal mold	Optional CR16, CR20, CR24, CR30, etc.
Shell removal pressure	Generally within 0.4 tons
Overall dimensions	210*165*290mm(LX*W*H)
Equipment weight	12Kg
Machine size diagram	