

Automatic Hot Press 3 Ton 300X300Mm Oil Free Osha Light Curtain Optional

Item Number: XP72



Introduction

This precision servo-driven automatic hot press delivers 0-6000 lbs force, features 300x300mm dual heated platens, independent ramp/soak temperature control up to 300°C, oil-free servo actuator, and optional OSHA-compliant light curtain safety shield. Contact us for a quote today.

[Learn More](#)

Item	Description
Model	XP72
Capacity	0 - 6000 lbs / 2.7 Tons
Platen Size	300 x 300 mm
Temperature Range	0 - 300 °C
Power	4500 W / 4.5 kW
Dimensions	700 x 450 x 1100 mm
Weight	220 kg
Compliance	OSHA compliant

Item	Description
Model	XP72
Capacity	0 - 6000 lbs / 2.7 Tons
Platen Size	300 x 300 mm
Temperature Range	0 - 300 °C
Power	4500 W / 4.5 kW
Dimensions	700 x 450 x 1100 mm
Weight	220 kg
Compliance	OSHA compliant